

Portable generator P4500



Features and benefits

- 4000 watts running, 4500 watts peak
- 10 hour continuous operating time (at rated load)
- Manual start
- 11 HP, 4-stroke overhead valve engine
- Large 24.6 litre fuel tank
- Automatic "low-oil shutdown"
- Recoil start
- Heavy-duty cast iron cylinder sleeve
- Circuit breaker protection
- Dual element air cleaner
- Full perimeter safety frame
- Stable power via Automatic Voltage Regulation (AVR)
- 12V DC battery charging outlet
- Long range fuel tank with fuel level gauge
- Voltmeter
- Includes spark plug spanner and oil fill extension

Weight, size and sound level

Weight: 82 kg

Size: Length 680 mm, width 540 mm, height 550 mm

Sound: 76 dB(A) at 7 m

Application:


General purpose generator ideal for the farm or trade. Ideal for running multiple power tools at once up to a combined 4000 watts and starting up to a 1¼ hp electric motor

Models and ratings

AC rated output	4 kW	DC amperage	8.3 A
AC max output	4.5 kW	Engine displacement	337 cc
AC Voltage	230 V	Engine horsepower	11 HP
AC frequency	50 Hz	Fuel Type	Unleaded petrol
230 V AC rated amperage - Rated/max	17.4 A/19 A	Fuel tank capacity	24.6 L
DC voltage	12 V	Oil capacity	1.1 L

Ratings apply to altitudes up to 1000 ft (304.8 m), 85 °F (30 °C). Total power available will decrease 3.5% for each 1000 ft (304.8 m) above 1000 ft; 2.0% for each 10 °F (5.5 °C) increase in ambient temperature above 85 °F (30 °C).

Control panel



Options and accessories

Cummins wheel kit (P/N A028Y919).

Warranty

The Cummins P4500 generator set comes with a standard 1 year limited warranty.

After sale support

Genuine Cummins maintenance care parts and products:

For your ongoing satisfaction and the dependability of your Cummins portable generator set, Cummins Power Generation offers a complete line of parts available at your nearby Cummins Inc. dealer.

Easy to locate certified Cummins service and parts dealers:

Cummins Inc. serves customers in more than 160 countries through its network of 550 company-owned and independent distribution facilities and more than 5000 dealer locations throughout the world. To easily locate the certified Cummins Inc. service dealer visit www.cumminsonan.com. See your distributor for more information.



Contact your distributor/dealer for more information.

Cummins Power Generation (UK) Ltd
Unit 1, Stevern Way
Reynolds Industrial Park
Peterborough
PE1 5EL
Tel: +44 (0) 1733 406100
Fax: +44 (0) 1733 406101
www.cumminsonan.com

