

Inverter generator series P3200ie



Cummins Onan

Performance you rely on.™



Features and benefits

- 2800 watts running, 3200 watts peak
- 6.5 hour continuous operating time (at rated load)
- Electric start (recoil back-up)
- 7 HP, 4-stroke overhead camshaft engine
- Large 2.9 gallon fuel tank
- LED display
- 120 V 20 A GFCI protected duplex, 120 V 30 A twist lock receptacles, 12 V DC charging
- Multi-meter w/LED display - voltmeter, hour meter, frequency and overload condition
- Auto-power saver
- 4 wheels standard
- 2 year limited warranty
- Meets EPA, CSA standards
- Not for sale in California

Weight, size and sound level

Weight: 130 lbs (58.9 kg)
Size: Length 21 in (537 mm), width 19 in (482.6 mm), height 23 in (583 mm)
Sound: Readings at 7 m: 58 dB(A)

Models and ratings

AC rated output	2.8 kW/2800 W	DC voltage	12 V
AC max output	3.2 kW/3200 W	Engine horsepower	7
AC Voltage	120 V	Fuel tank capacity	2.9 Gal/10.9 L
AC frequency	60 Hz		
120 V AC rated amperage - Rated/max	23.3 A/26.7 A		

Ratings apply to altitudes up to 1000 ft (304.8 m), 85 °F (30 °C). Total power available will decrease 3.5% for each 1000 ft (304.8 m) above 1000 ft and 2.0% for each 10 °F (5.5 °C) increase in ambient temperature above 85 °F (30 °C).

©2009 Cummins Power Generation. Cummins®, Onan®, the "C" logo and Performance you rely on.™ are servicemarks, trademarks and/or registered trademarks of Cummins Inc. All Rights Reserved. Specifications are subject to change without notice.
A-1504b (3/09) (formerly F-1669)

Warranty

The Cummins Onan P3200ie inverter generator comes with a standard 2 year limited warranty.



After sale support

Genuine Cummins Onan maintenance care parts and products:

For your ongoing satisfaction and the dependability of your Cummins Onan portable generator set, Cummins Power Generation offers a complete line of parts available at your nearby Cummins Onan dealer.

Easy to locate certified Cummins Onan service and parts dealers:

Cummins Power Generation has trained, tested and certified over 1000 authorized Cummins Onan Service Dealers covering most major metropolitan areas in the U.S. and Canada. To easily locate the certified Cummins Onan Service Dealer nearest you, visit www.cumminsonan.com or look in the yellow pages under "generator sets, electric". See your distributor for more information.

Contact your distributor/dealer for more information.

Cummins Onan

Cummins Power Generation
1400 73rd Ave. NE
Minneapolis, MN 55432 USA
Phone 1 763 574 5000
Toll-free 1 800 344 0039 24/7 CUST SVC.
Fax 1 763 574 5298
Email www.cumminsonan.com/contact
www.cumminsonan.com

