

REL NO	LTR	NO	REVISION	DWN	CKD	APVD	DATE
ECO-102845	G	1	REVISED "SQUARE D" TABLE	AWG	JM	L. SMITH	16DEC08

SPECIAL WITHSTAND RATINGS

Circuit Breaker Protection
When protected by one of the following circuit breakers rated not more than 225 amperes, this transfer switch is rated for use on a circuit capable of delivering not more than the indicated RMS symmetrical amperes at the voltage shown.

GE

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
AKRU, AKU	200000	200000	200000
FB, FC	200000	150000	42000
SEL, SFL	100000	50000	25000
SEP, SFP	200000	50000	25000
TEC, TECL	100000	100000	100000
TEL, TEML, TFL	100000	65000	25000
THLC1, THLC2	200000	200000	50000

Siemens

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
CED6, CFD6	200000	200000	100000
CJD6, SCJD6	200000	150000	100000

Square D

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
F1, K1	200000	200000	100000
HD, JD	25000	18000	14000
HG, JG	65000	35000	18000
HJ, JJ	100000	65000	25000
HL, JL	125000	100000	50000

Westinghouse/Cutler-Hammer

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
DSL, FB, LA	200000	200000	200000
FCL	200000	150000	-
FDC, JDC	200000	100000	35000
KDC	200000	100000	50000
LCL	200000	200000	100000

Merlin Gerin

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
CE106L	150000	100000	42000
CF250L	150000	150000	30000
NSE100N	65000	18000	-
NSF150N, NSF250N	65000	35000	18000
NSF150H, NSF250H	100000	65000	25000

0098-6918.G

193.80



73.15

USE FOR INTERNAL CONTROL ONLY
THIS DOCUMENT IS CONTROLLED TO MAINTAIN COMPLIANCE WITH CODES AND STANDARDS:
 UL CSA US TESTING OTHER
AND/OR TO RETAIN DESIGN RESPONSIBILITY.
ANY CHANGES OR DEVIATIONS TO THIS DOCUMENT MUST BE APPROVED BY THE COORDINATOR LISTED.
FACILITY FRIDLEY DATE 8-23-96
SIGNATURE D.C. KAMNETZ
FACILITY _____ DATE _____
SIGNATURE _____

NOTES:

- LABEL SHOWN ON PRINT IS NOT ARTWORK. VENDOR ARTWORK CREATED TO PRODUCE THIS LABEL MUST BE SIGNED OFF BY CUMMINS POWER GENERATION PURCHASING.
- ALL TEXT TO BE HELVETICA SANS SERIF, OR EQUIVALENT.
- ALL COLORS PER ANSI Z535.1. DANGER---RED BACKGROUND, WITH WHITE COPY CAUTION---YELLOW BACKGROUND, WITH BLACK COPY WARNING---ORANGE BACKGROUND, WITH BLACK COPY
- SEE ONAN MATERIAL SPECIFICATION FOR APPLICATION INFORMATION.
- IF CORNERS SHOWN SQUARE, RADIUS OPTIONAL.
- IF CSA AGENCY APPROVAL REQUIRED (SEE TABULATION), LOCATE VENDOR CSA IDENTIFICATION MARK IN LOWER RIGHT HAND CORNER.
- LOCATE LABEL PART NUMBER & REVISION LETTER EITHER WHERE SHOWN, OR IN LOWER LEFT HAND CORNER.

TABULATION						
DRAWING NO.	CURRENT ER NO.	MATERIAL (SEE NOTE 4)	AGENCY APPROVAL	MATERIAL THICKNESS	BACKGROUND COLOR	TEXT COLOR
0098-6918	ECO-102845	MS20111	UL, CSA	10 ml	WHITE	BLACK

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS		SIM TO _____		DWN <u>A. GOETZ</u>		 CUMMINS POWER GENERATION	
DO NOT SCALE PRINT				CKD <u>J. MORLEY</u>			
DIM	X ± 1	HOLE	0.00- 4.99 +0.15/-0.08	APVD <u>L. SMITH</u>		LABEL-SPCL BREAKER SITE CODE PGF	
	.X ± 0.8		5.00- 9.99 +0.20/-0.10	DATE <u>16DEC08</u>			
	.XX ± 0.38		10.00-17.49 +0.25/-0.13	FOR INTERPRETATION OF DIMENSIONING AND TOLERANCING, SEE ASME Y14.5M-1994			
ANG TOL: ± 1.0°		SCALE: 1/1		FIRST USED ON <u>OT 40-125 AMP</u>		DWG SIZE B	0098_6918
				PROPERTY OF CUMMINS POWER GENERATION GROUP		SHEET 1 OF 1	DWG REV G

Part A004C487 G

Description	Legacy Name	External Regulations	Application Status	Release Phase Code	Security Classification	Alternates
LABEL	0098-6918	UL,CSA	Production Only	Production	Proprietary	

Part Specifications :A004C487 G

Name	Description	Legacy Name
A004S008	SPECIFICATION,MATERIAL	0MS2-0111
A010Z301	DRAWING,ENGINEERING	0098-6918