

REL NO	LTR	NO	REVISION	DWN	CKD	APVD	DATE
ECO-102858	G	I	REVISED "SQUARE D" TABLE	AWG	JM	L_SMITH	12AUG09

73.2

**SPECIAL WITHSTAND RATINGS**

**Circuit Breaker Protection**

When protected by one of the following circuit breakers rated not more than 400 amperes, this transfer switch is rated for use on a circuit capable of delivering not more than the indicated RMS symmetrical amperes at the voltage shown.

**GE**

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
AKRU, AKU	200000	200000	200000
FB, FC	200000	150000	42000
SEL, SFL	100000	65000	25000
SEP, SFP	200000	100000	25000
SGL	100000	65000	65000
SGP	200000	100000	65000
TEC, TECL	100000	100000	100000
TEL, TEML, TFL	100000	65000	25000
THLC1, THLC2, THLC4	200000	200000	50000

**Siemens**

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
CE06, CF06	200000	200000	100000
CJ06, CL06	200000	150000	100000
SCJ06, SCL06	200000	150000	100000

**Square D**

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
DG, HG, JG	65000	35000	18000
DJ, HJ, JJ	100000	65000	25000
DL	125000	100000	25000
FI, KI, LI	200000	200000	100000
HD, JD	25000	18000	14000
HL, JL	125000	100000	50000

**Westinghouse/Cutler-Hammer**

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
DSL, LA, NB	200000	200000	200000
FDC, JDC	200000	100000	35000
KDC, LDC	200000	100000	50000
LCL	200000	200000	100000

**Merlin Gerin**

TYPE	Interrupting Rating at		
	240 VAC	480 VAC	600 VAC
CE106L	150000	100000	42000
CF250L, CJ400L	150000	150000	65000
CK1000L	150000	50000	42000
NSE100N	65000	18000	-
NSF150N, NSF250N	65000	35000	18000
NSF150H, NSF250H	100000	65000	25000
NSJ400N, NSJ600N	65000	35000	18000
NSJ400H, NSJ600H	100000	65000	25000
NSJ400L, NSJ600L	150000	100000	25000

0098-6919.G

228.6

\* DIMS ARE METRIC

USE FOR INTERNAL CONTROL ONLY  
 THIS DOCUMENT IS CONTROLLED TO MAINTAIN COMPLIANCE WITH CODES AND STANDARDS:  
 UL  CSA  US TESTING  OTHER  
 AND/OR TO RETAIN DESIGN RESPONSIBILITY.   
 ANY CHANGES OR DEVIATIONS TO THIS DOCUMENT MUST BE APPROVED BY THE COORDINATOR LISTED.  
 FACILITY: FRIDLEY DATE: 8-23-96  
 SIGNATURE: D.C. KAMNETZ  
 FACILITY: \_\_\_\_\_ DATE: \_\_\_\_\_  
 SIGNATURE: \_\_\_\_\_

NOTES:

- LABEL SHOWN ON PRINT IS NOT ARTWORK. VENDOR ARTWORK CREATED TO PRODUCE THIS LABEL MUST BE SIGNED OFF BY CUMMINS POWER GENERATION PURCHASING.
- ALL TEXT TO BE HELVETICA SANS SERIF, OR EQUIVALENT.
- ALL COLORS PER ANSI Z535.1. DANGER---RED BACKGROUND, WITH WHITE COPY CAUTION---YELLOW BACKGROUND, WITH BLACK COPY WARNING---ORANGE BACKGROUND, WITH BLACK COPY
- SEE ONAN MATERIAL SPECIFICATION FOR APPLICATION INFORMATION.
- IF CORNERS SHOWN SQUARE, RADIUS OPTIONAL.
- IF CSA AGENCY APPROVAL REQUIRED (SEE TABULATION), LOCATE VENDOR CSA IDENTIFICATION MARK IN LOWER RIGHT HAND CORNER.
- LOCATE LABEL PART NUMBER & REVISION LETTER EITHER WHERE SHOWN, OR IN LOWER LEFT HAND CORNER.

DRAWING NO.	CURRENT ER NO.	MATERIAL (SEE NOTE 4)	TABULATION			
			AGENCY APPROVAL	MATERIAL THICKNESS	BACKGROUND COLOR	TEXT COLOR
0098-6919	ECO-102858	MS20111	UL, CSA	10 ml	WHITE	BLACK

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS		SIM TO	DWN T.A. SORENSEN		<b>CUMMINS POWER GENERATION</b>	
DO NOT SCALE PRINT			CKD JIM_OLSON		LABEL-SPCL BREAKER	
DIM	X ± 1	HOLE	APVD L_SMITH	SITE CODE	PGF	SHEET 1 OF 1
	.X ± 0.8		DATE 12JAN94			
	.XX ± 0.38		FOR INTERPRETATION OF DIMENSIONING AND TOLERANCING, SEE ASME Y14.5M-1994	FIRST USED ON OT/BT 150-260 A	0098_6919	DWG REV G
ANG TOL: ± 1.0°		SCALE: 1/1				

**Part A004C488 G**

Description	Legacy Name	External Regulations	Application Status	Release Phase Code	Security Classification	Alternates
LABEL	0098-6919	UL,CSA	Production Only	Production	Proprietary	

---

**Part Specifications :A004C488 G**

Name	Description	Legacy Name
A004S008	SPECIFICATION,MATERIAL	0MS2-0111
A010Z302	DRAWING,ENGINEERING	0098-6919