



Spark ignited generator set 85 kW standby



Features and benefits

- Extremely quiet operation
- Fully automatic operation when used with a Cummins Onan automatic transfer panel
- Available for use with natural gas or LP vapor
- Attractive and discreet sound attenuated housing
- Electronic governor for precise frequency control
- Includes 120 V coolant heater
- Listed to UL 2200
- EPA certified for dual fuel
- Aluminum or steel enclosure for best anti-corrosion performance
- IBC and OSHPD seismic certified

Size and sound level

Size: Length 142 in (3614 mm), width 60 in (1520 mm), height 70 in (1789 mm)

Sound: 72 dB(A) measured at 7 m, average at full load with aluminum enclosure;
70 dB(A) measured at 7 m, average at full load with steel enclosure

Models and ratings

Order model	Fuel	Voltage	Phase	Rated kW	kVA	Rated amps	Circuit breaker	Enclosure
GGHG	Natural gas/ Propane	120/240	1	85	85	708.3/345.2	400 A, 2 pole	Aluminum or steel
	Natural gas/ Propane	120/208	3	85	85	511.8/295.3	400 A, 3 pole	Aluminum or steel

Note: See page 4 of this document for derating factors.

Standard features

Engine:

- Electronic ignition
- Electronic governor
- Full-pressure lubrication
- High-capacity oil sump, spin-on oil filter
- Solenoid shift starter
- 65 A, engine-driven battery charger
- 120 V coolant heater
- Oil drain extension

Control system:

- PCC 2100 control system
- Automatic remote starting
- Controls generator set starting and shutdown
- Control components designed to withstand the vibration levels typical in generator sets
- Field circuit breaker
- High temperature, low oil pressure, low coolant level, overcrank and over speed shutdowns
- Running time meter
- UL Listed circuit breaker
- DC control fuse

Exhaust muffler:

- Enclosed exhaust silencer
- Low noise

Engine details

Engine: Ford industrial, spark-ignited

Design: 10-cylinder V, liquid-cooled, turbocharged

Compression ratio: 9.0 to 1

Displacement: 415 cu in (6.8 L)

Cooling system: 122° F (50 °C) ambient cooling system

Oil sump capacity, L (qt): 6.1 (6.5)

Operating speed: 1800 RPM

Gross engine power output, kWm (bhp):

Model	Natural Gas	Propane
GGHG	131.3 (176.0)	122.3 (164.0)

Genset weight:

Model	Enclosure	Weight lbs (kg)
GGHG	Aluminum	2925 (1327)
	Steel	3240 (1470)

Average fuel consumption

Fuel consumption – natural gas - GGHG

Load:	1/4	1/2	3/4	Full
Ft ³ /hr	418.9	614.1	833.0	1090.1
M ³ /hr:	11.9	17.4	23.6	30.9

Fuel consumption – propane - GGHG

Load:	1/4	1/2	3/4	Full
Ft ³ /hr	162.3	241.6	326.5	415.0
M ³ /hr:	4.6	6.8	9.2	11.7

Alternator details

Design: Brushless, revolving field, 12 lead re-connectable, single phase design.

Insulation system: Class H per NEMA MG1-1.65.

Temperature rise: At rated load is less than 125 °C at standby rating, per NEMA MG1.22.40, IEEE 115 and IEC 34-1.

Exciter type: The excitation system derives its power from the main output of the generator, eliminating the need for a separate excitation power source.

Alternator cooling: Direct drive centrifugal blower.

Rotor: Supported by a pre-lubricated maintenance-free ball bearing.

AC wave form total harmonic distortion: Less than 5% total no load to full load, less than 3% for any single harmonic.

Generator set performance

Governor regulation class: ISO 8528 Part 1 Class G3

Voltage regulation: 1%, no load to full load.


Frequency regulation: Isochronous, 0% no load to full load.

Operating temperature: -20 °F (-28.8 °C) to 122 °F (50 °C).

Motor starting kVA (at 90% sustained voltage):
GGHG: 250, GGHH: 305


Basic dimensions

Dimensions: mm/in



Note: This outline drawing is provided for general reference only and is not intended for design or installation. For more information see Operation and Installation manuals.

Automatic transfer panel configurations



Options and accessories

- Battery, 12 V, 620 cca (P/N 416-0823)
- Battery heater kit (P/N 333-0469)
- Full line of complementing automatic transfer panels

Housing features

- Sound attenuated, weather protective design, key-lockable service access doors
- Internal starting battery tray and tie down
- Heavy-duty aluminum or steel housing, stainless steel fasteners

Our energy working for you.™

©2015 Cummins Inc. | A-1562e (8/15)

power.cummins.com
cumminsonan.com

Derating factors

85GGHG Model, Natural Gas

Engine power available up to 1554 m (5100 ft) at ambient temperatures up to 40 °C (104 °F). Above 1554 m (5100 ft) derate at 4% per 305 m (1000 ft), and 2% per 11 °C (1% per 10 °F) above 40 °C (104 °F).

85GGHG Model, Propane

Engine power available up to 1097 m (3600 ft) at ambient temperatures up to 40 °C (104 °F). Above 1097 m (3600 ft) derate at 4% per 305 m (1000 ft), and 2% per 11 °C (1% per 10 °F) above 40 °C (104 °F).

Testing and standards



This generator set is designed in facilities certified to ISO 9001 and manufactured in facilities certified to ISO 9001 or ISO 9002.



All low voltage models are CSA certified to product class 4215-01.



The generator set is available Listed to UL 2200, Stationary Engine Generator Assemblies. The PowerCommand control is Listed to UL 508 - Category NITW7 for U.S. and Canadian usage.

U.S. EPA

Engine certified to U.S. EPA SI Stationary Emergency Emission Regulation 40 CFR, Part 60.

After sale support

Largest distributor/dealer support network

Cummins generator sets are supported by the largest and best trained worldwide certified distributor/dealer network in the industry. This network of knowledgeable Cummins distributor/dealers will help you select and install the right generator set and accessories to meet the requirements of your specific application. This same network offers a complete selection of commonly used generator set maintenance parts, accessories and products plus manuals and specification sheets. Plus, they can answer your questions regarding proper operation, maintenance schedules and more.

Manuals: Operation and installation manuals ship with the generator set. To obtain additional copies or other manuals for this model, see your Cummins distributor/dealer.

To easily locate the nearest Cummins distributor/dealer in your area, visit www.cumminsonan.com or www.cumminspower.com.

Warranty policy

Cummins generators come with a standard two-year warranty. Additional two and five-year warranty options are available. Some restrictions apply.

This product is EPA Emissions certified for emergency standby use only.



WARNING:

Standby rating based on: Applicable for supplying emergency power for the duration of normal power interruption. No sustained overload capability is available for this rating. (Equivalent to fuel stop power in accordance with ISO3046, AS2789, DIN6271 and BS5514.) nominally rated.



WARNING:

Back feed to a utility system can cause electrocution and/or property damage. Do not connect to any building electrical except through an approved device or after building main breaker is open.

Contact your distributor/dealer for more information.

North America
1400 73rd Avenue N.E.
Minneapolis, MN 55432
USA

Phone 763 574 5000
Fax 763 574 5298

Our energy working for you.™

©2015 Cummins Inc. All rights reserved.

Cummins is a registered trademark of Cummins Inc.

"Our energy working for you." is a trademark of Cummins Power Generation. Other company, product, or service names may be trademarks or service marks of others. Specifications are subject to change without notice.

A-1562e (8/15)



power.cummins.com
cumminsonan.com