

# Tier4 certified diesel generator set QST30 series engine

900 - 1000 kW 60 Hz



## **Description**

Cummins® commercial generator sets are fully integrated power generation systems providing optimum performance, reliability and versatility for stationary Standby and Prime Power applications.

#### **Features**

**Cummins heavy-duty engine** - Rugged 4-cycle, industrial diesel delivers reliable power, low emissions and fast response to load changes.

**Alternator** - Several alternator sizes offer selectable motor starting capability with low reactance 2/3 pitch windings, low waveform distortion with non-linear loads and fault clearing short-circuit capability.

Cummins aftertreatment system - Fully integrated power generation systems that are certified to EPA Tier 4 standards. They provide optimum performance, reliability and versatility for stationary Standby, Prime Power and Continuous duty applications.

**Permanent Magnet Generator (PMG)** - Offers enhanced motor starting and fault clearing short-circuit capability.

Control system - The PowerCommand® electronic control is standard equipment and provides total genset system integration including automatic remote starting/stopping, precise frequency and voltage regulation, alarm and status message display, AmpSentry™ protection, output metering, auto-shutdown at fault detection and NFPA 110 Level 1 compliance.

**Cooling system** - Standard integral set-mounted radiator system, designed and tested for rated ambient temperatures, simplifies facility design requirements for rejected heat.

**NFPA** - The genset accepts full rated load in a single step in accordance with NFPA 110 for Level 1 systems.

**Warranty and service** - Backed by a comprehensive warranty and worldwide distributor network.

	Standby rating	Prime rating	Emissions compliance	Data sheets
Model	60 Hz kW (kVA)	60 Hz kW (kVA)	EPA	60 Hz
DQFAH	1000 (1250)	900 (1125)	T4F certified	D-3535

# **Generator set specifications**

Governor regulation class	ISO8528 Part 1 Class G3		
Voltage regulation, no load to full load	+/- 0.5%		
Random voltage variation	+/- 0.5%		
Frequency regulation	Isochronous		
Random frequency variation	+/- 0.25%		
Radio frequency emissions compliance	IEC 61000-4-2 : Level 4 Electrostatic discharge IEC 61000-4-3 : Level 3 Radiated susceptibility		

# **Engine specifications**

Bore	140 mm (5.51 in)		
Stroke	165.0 mm (6.5 in)		
Displacement	30.5 litres (1860 in <sup>3</sup> )		
Configuration	Cast iron, V, 12 cylinder		
Battery capacity	1800 amps minimum at ambient temperature of -18 °C to 0 °C (0 °F to 32 °F)		
Battery charging alternator	35 amps		
Starting voltage	24 volt, negative ground		
Fuel system	Direct injection: number 2 diesel fuel, fuel filter, automatic electric fuel shutoff		
Fuel filter	Triple element, 10 micron filtration, spin-on fuel filters with water separator		
Air cleaner type	Dry replaceable element		
Lube oil filter type(s)	Four spin-on, combination full flow filter and bypass filters		
Standard cooling system	High ambient radiator		

# **Aftertreatment specifications**

A troi ir oddinoni o poomodiio			
Model	CA451		
Emissions certification	Tier4F certified		
Duct diameter	1143 mm (45 in)		
Duct quantity	1		
Components included	Insulated aftertreatment ducts, saddle supports for aftertreatment, control panel, DEF tank, heater with ILB, harness from control panel to engine and AFT, lifting tool. Assembly required at site.		

# **Alternator specifications**

Design	Brushless, 4 pole, drip proof, revolving field		
Stator	2/3 pitch		
Rotor	Single bearing, flexible disc		
Insulation system	Class H on low and medium voltage, Class F on high voltage		
Standard temperature rise	150 °C Standby at 40 °C ambient		
Exciter type Permanent Magnet Generator (PMG)			
Phase rotation	A (U), B (V), C (W)		
Alternator cooling	Direct drive centrifugal blower fan		
AC waveform Total Harmonic Distortion (THDV)	< 5% no load to full linear load, < 3% for any single harmonic		
Telephone Influence Factor (TIF)	< 50% per NEMA MG1-22.43		
Telephone Harmonic Factor (THF)	< 3%		

# **Available voltages**

• 120/208 • 220/380 • 240/416 • 277/480

• 139/240 • 230/400 • 255/440 • 347/600

Note: Consult factory for other voltages.

# Generator set options and accessories

#### **Engine**

- 208/240/480 V coolant heater for ambient above 4.5 °C (40 °F)
- 208/240/480 V coolant heater for ambient below 4.5 °C (40 °F)

## **Control panel**

- 120/240 V 100 W control anticondensation heater
- Paralleling configuration
- Remote fault signal package
- Run relay package

#### **Alternator**

- 80 °C rise
- 105 °C rise
- 125 °C rise
- 120/240 V 300 W, anti-condensation heater

- Temperature sensor RTDs, 2phase
- Temperature sensor alternator bearing RTD
- Differential current transformers

#### Aftertreatment system

- DEF lines
- DEF freeze protection kit
- SCR only
- SCR w/heater (ILB)
- SCR w/heater and DPF Configuration

## Cooling system

Remote radiator

#### Generator set

- AC entrance box
- Battery
- Battery rack with hold-down floor standing
- Circuit breaker set mounted
- Disconnect switch set mounted
- PowerCommand network
- Remote annunciator panel
- Spring isolators
- 2 year warranty
- 5 year warranty
- 10 year major components warranty

Note: Some options may not be available on all models - consult factory for availability.

# **PowerCommand 3.3 Control System**



An integrated microprocessor based generator set control system providing voltage regulation, engine protection, alternator protection, operator interface and isochronous governing. Refer to document S-1570 for more detailed information on the control.

**AmpSentry** – Includes integral AmpSentry protection, which provides a full range of alternator protection functions that are matched to the alternator provided.

**Power management** – Control function provides battery monitoring and testing features and smart starting control system.

**Advanced control methodology** – Three phase sensing, full wave rectified voltage regulation, with a PWM output for stable operation with all load types.

**Communications interface** – Control comes standard with PCCNet and Modbus interface.

**Regulation compliant** – Prototype tested: UL, CSA and CE compliant.

**Service** - InPower™ PC-based service tool available for detailed diagnostics, setup, data logging and fault simulation.

**Easily upgradeable** – PowerCommand controls are designed with common control interfaces.

Reliable design – The control system is designed for reliable operation in harsh environment.

Multi-language support

#### **Operator panel features**

#### Operator/display functions

- Displays paralleling breaker status
- Provides direct control of the paralleling breaker
- 320 x 240 pixels graphic LED backlight LCD
- Auto, manual, start, stop, fault reset and lamp test/panel lamp switches
- Alpha-numeric display with pushbuttons
- LED lamps indicating generator set running, remote start, not in auto, common shutdown, common warning, manual run mode, auto mode and stop

#### Paralleling control functions

- First Start Sensor System selects first generator set to close to bus
- Phase Lock Loop Synchronizer with voltage matching
- Sync check relay
- Isochronous kW and kVar load sharing
- Load govern control for utility paralleling
- Extended Paralleling (baseload/peak shave) Mode
- Digital power transfer control, for use with a breaker pair to provide open transition, closed transition, ramping closed transition, peaking and base load functions,

#### Alternator data

- Line-to-neutral and line-to-line AC volts
- 3-phase AC current
- Frequency
- kW, kvar, power factor kVA (three phase and total)

#### **Engine data**

- DC voltage
- Engine speed
- Lube oil pressure and temperature
- Coolant temperature
- Comprehensive FAE data (where applicable)

#### Other data

- Genset model data
- Start attempts, starts, running hours, kW hours
- Load profile (operating hours at % load in 5% increments)
- Fault history
- Data logging and fault simulation (requires InPower)

#### Standard control functions

## Digital governing

- Integrated digital electronic isochronous governor
- Temperature dynamic governing

#### Digital voltage regulation

- Integrated digital electronic voltage regulator
- 3-phase, 4-wire line-to-line sensing
- · Configurable torque matching

#### **AmpSentry AC protection**

- AmpSentry protective relay
- Over current and short circuit shutdown
- Over current warning
- Single and three phase fault regulation
- Over and under voltage shutdown
- Over and under frequency shutdown
- Overload warning with alarm contact
- Reverse power and reverse var shutdown
- · Field overload shutdown

#### **Engine protection**


- · Battery voltage monitoring, protection and testing
- Overspeed shutdown
- · Low oil pressure warning and shutdown
- High coolant temperature warning and shutdown
- Low coolant level warning or shutdown
- Low coolant temperature warning
- Fail to start (overcrank) shutdown
- Fail to crank shutdown
- · Cranking lockout
- Sensor failure indication
- Low fuel level warning or shutdown
- Fuel-in-rupture-basin warning or shutdown
- Full authority electronic engine protection


#### **Control functions**

- · Time delay start and cool down
- Real time clock for fault and event time stamping
- Exerciser clock and time of day start/stop
- Data logging
- · Cycle cranking
- Load shed
- Configurable inputs and outputs (4)
- Remote emergency stop

#### **Options**

• Auxiliary output relays (2)







# **Generator set weights and dimensions**

\* Weights represent a set with standard features. See outline drawings for weights of other configurations.

Model	Dim "A"	Dim "B"	Dim "C"	Set weight*	Set weight*
	mm (in.)	mm (in.)	mm (in.)	dry kg (lbs)	wet kg (lbs)
DQFAH	4239 (167)	2000 (79)	2353 (93)	7631 (16824)	7929 (17480)





# Aftertreatment weights and dimensions

\* Due to multiple configurations of the CA451 model, maximum weight of the model is shown. Note: Dimension and weights are subject to change. See submittal data for exact details.

Aftertreatment model number*	Genset model	L (Length) mm (in.)	W (Width) mm (in.)	H (Height) mm (in.)	Weight of aftertreatment system (lbs)
CA451	DQFAH	4651 (183)	1480 (58)	1260 (50)	4367

## Codes and standards

Codes or standards compliance may not be available with all model configurations – consult factory for availability.

<b>(</b>	All low and medium voltage models are CSA certified to product class 4215-01.	ISO8528	The generator set has been rated in accordance with ISO8528.
U.S. EPA	Engine certified to US EPA Nonroad 40CFR1039 and Stationary (Emergency and Non-Emergency) US EPA NSPS, 60CFR Subpart IIII Tier4 Emissions Standards.	150 9001	This generator set is designed in facilities certified to ISO 9001 and manufactured in facilities certified to ISO 9001 or ISO 9002.
International Building Code	The genset package is certified for seismic application in accordance with the following International Building Code: IBC2012.	central us Intertek	The Aftertreatment System bears the ETL ListedMark as proof of conformity to NFPA 79, UL 61010C-1, and CSA 22.2 No. 61010-1-12.
PTS	The Prototype Test Support (PTS) program verifies the performance integrity of the generator set design. Cummins products bearing the PTS symbol meet the prototype test requirements of NFPA 110 for Level 1 systems.		The generator set is available listed to UL 2200 for all 60 Hz low voltage models, Stationary Engine Generator Assemblies. The PowerCommand control is Listed to UL 508 - Category NITW7 for U.S. and Canadian usage. Circuit breaker assemblies are UL 489 Listed for 100% continuous operation and also UL 869A Listed Service Equipment.

**Warning:** Back feed to a utility system can cause electrocution and/or property damage. Do not connect to any building's electrical system except through an approved device or after building main switch is open.

For more information contact your local Cummins distributor or visit power.cummins.com



#### Our energy working for you.™