

Generator set data sheet

1350 kW (1688 kVA) Standby



Model: C1350 N6
Frequency: 60 Hz
Fuel type: Natural gas MI 78 +
Emissions NOx: 1.0 g/hp-hr
LT water inlet temp: 50°C (122°F)
HT water outlet temp: 90°C (194°F)

Measured sound performance data sheet:	MSP-1007
Prototype test summary data:	PTS-158
Remote radiator cooling outline:	0500-5090

Fuel consumption (ISO3046/1)	See Note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
Fuel consumption (LHV) ISO3046/1, kW (MMBTU/hr)	2,4,6,7	3803 (12.99)	3457 (11.81)	2950 (10.07)	2096 (7.16)
Mechanical efficiency ISO3046/1	2,4,7	38.2%	37.8%	37.0%	35.0%
Electrical efficiency ISO3046/1	2,4,6,7	36.8%	36.5%	35.6%	33.4%

Engine

Engine manufacturer	Cummins
Engine model	QSK60G
Configuration	V16
Displacement, L (cu.in)	60.3 (3683)
Aspiration	Turbocharged (2)
Gross engine power output, kWm (hp)	1454 (1949)
BMEP, bar (psi)	16.1 (233)
Bore, mm (in)	159 (6.26)
Stroke, mm (in)	190 (7.48)
Rated speed, rpm	1800
Piston speed, m/s (ft/min)	11.4 (2244)
Compression ratio	11.4:1
Lube oil capacity, L (qt)	380 (401)
Overspeed limit, rpm	2070
Full load lubricating oil consumption, g/kWe-hr (g/hp-hr)	0.15 (0.11)

Fuel

Gas supply pressure to engine inlet, bar (psi) ⁷	0.26 (3.8)
Min methane index	78

Starting system(s)

Electric starter voltage, volts	24
Min battery capacity @ 40°C (104°F), AH	450
Air starter pressure, barg (psig)	N/A
Air starter flow, Nm ³ /s (scfm)	N/A

Genset dimensions (see Note 1)

Genset length, m (ft)	5.00 (16.39)
Genset width, m (ft)	2.33 (7.64)
Genset height, m (ft)	2.97 (9.75)
Genset weight (wet), kg (lbs)	13924 (30697)

Energy data

	See Note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
Continuous generator electrical output, kWe @ 1.0 pf	10	1400	1260	1050	700
Heat dissipated in lube oil cooler, kW (MMBTU/h)	5	255 (0.87)	240 (0.82)	219 (0.75)	190 (0.65)
Heat dissipated in block, kW (MMBTU/h)	5	447 (1.53)	420 (1.43)	371 (1.27)	281 (0.96)
Total heat rejected in LT circuit, kW (MMBTU/h)	5	127 (0.43)	113 (0.39)	95 (0.32)	75 (0.26)
Total heat rejected in HT circuit, kW (MMBTU/h)	5	927 (3.16)	846 (2.89)	715 (2.44)	509 (1.74)
Unburnt, kW (MMBTU/h)	13	97 (0.33)	93 (0.32)	80 (0.27)	52 (0.18)
Heat radiated to ambient, kW (MMBTU/h)	13	177 (0.60)	163 (0.56)	149 (0.51)	127 (0.43)
Available exhaust heat to 105C, kW (MMBTU/h)	5	975 (3.33)	896 (3.06)	783 (2.67)	574 (1.96)

Intake air flow

Intake air flow mass, kg/s (lb/hr)	4	2.33 (18487)	2.11 (16708)	1.78 (14118)	1.23 (9777)
Intake air flow volume, m ³ /s @ 0°C (scfm)	4	1.80 (4031)	1.63 (3643)	1.38 (3078)	0.95 (2132)
Max air cleaner restriction, mmHG (in H ₂ O)		18 (9.8)	18 (9.8)	18 (9.8)	18 (9.8)

Exhaust air flow

Exhaust gas flow mass, kg/s (lb/hr)	4	2.42 (19147)	2.19 (17308)	1.85 (14628)	1.28 (10138)
Exhaust gas flow volume, m ³ /s (cfm)	4	5.17 (10945)	4.71 (9972)	4.05 (8572)	2.89 (6117)
Exhaust temperature after turbine, °C (°F)	6	482 (900)	488 (910)	501 (934)	524 (975)
Max exhaust system back pressure, mmHG (in H ₂ O)	6,14	37.3 (20.0)	37.3 (20.0)	37.3 (20.0)	37.3 (20.0)
Min exhaust system back pressure, mmHG (in H ₂ O)	6,14	N/A	N/A	N/A	N/A

HT cooling circuit

HT circuit engine coolant volume, l (gal)		181 (48)	181 (48)	181 (48)	181 (48)
HT coolant flow @ max ext restriction, m ³ /h (gal/min)		83 (365)	83 (365)	83 (365)	83 (365)
Max HT engine coolant inlet temp, °C (°F)	8	80 (176)	80 (176)	80 (176)	80 (176)
HT coolant outlet temp, °C (°F)	8	90 (194)	90 (194)	90 (194)	90 (194)
Max pressure drop in external HT circuit, bar (psig)		1.00 (15)	1.00 (15)	1.00 (15)	1.00 (15)
HT circuit max pressure, bar (psig)		4.5 (65)	4.5 (65)	4.5 (65)	4.5 (65)
Min static head, bar (psig)		0.5 (7)	0.5 (7)	0.5 (7)	0.5 (7)

LT cooling circuit	See Note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
LT circuit engine coolant volume, l (gal)		34 (9)	34 (9)	34 (9)	34 (9)
LT coolant flow @ max ext restriction, m ³ /h (gal/min)		29 (125)	29 (125)	29 (125)	29 (125)
Max LT engine coolant inlet temp, °C (°F)	9	50 (122)	50 (122)	50 (122)	50 (122)
LT coolant outlet temp, °C (°F) reference only	9	54.0 (129)	54.0 (129)	54.0 (129)	54.0 (129)
Max pressure drop in external LT circuit, bar (psig)		1.00 (15)	1.00 (15)	1.00 (15)	1.00 (15)
LT circuit max pressure, bar (psig)		4.5 (65)	4.5 (65)	4.5 (65)	4.5 (65)
Min static head, bar (psig)		0.5 (7)	0.5 (7)	0.5 (7)	0.5 (7)

Emissions

NO _x emissions wet, ppm	5	169	164	158	178
NO _x emissions, mg/Nm ³ @ 5% O ₂ (g/hp-h)	5	473 (1.07)	459 (1.04)	437 (1.02)	480 (1.19)
THC emissions wet, ppm	13	1357	1443	1484	1395
THC emissions, mg/Nm ³ @ 5% O ₂ (g/hp-h)	13	1496 (3.40)	1581 (3.63)	1616 (3.78)	1483 (3.70)
CO emissions (dry), ppm	13	419	416	406	405
CO emissions rate at exhaust, mg/Nm ³ (g/hp-h)	13	485 (1.64)	474 (1.62)	459 (1.60)	440 (1.63)
O ₂ emissions (dry), percent	13	9.3	9.2	9.1	8.8
Particulates PM10, g/hp-h	13	< 0.03	< 0.03	< 0.03	< 0.03

Genset de-rating

Altitude and temperature derate multiplication factor

Barometer		Altitude		Table A *								
In Hg	mbar	Feet	Meters	Derate multiplier off grid (island or load share)								
20.7	701	9843	3000	0.67	0.66	0.64	0.63	0.62	0.58	0.55	0.52	-
21.4	723	9022	2750	0.70	0.69	0.67	0.66	0.65	0.62	0.58	0.55	0.52
22.1	747	8202	2500	0.73	0.72	0.71	0.69	0.68	0.65	0.61	0.58	0.55
22.8	771	7382	2250	0.76	0.75	0.74	0.72	0.71	0.68	0.65	0.61	0.58
23.5	795	6562	2000	0.80	0.78	0.77	0.76	0.74	0.71	0.68	0.65	0.61
24.3	820	5741	1750	0.83	0.81	0.80	0.79	0.77	0.74	0.71	0.68	0.64
25.0	846	4921	1500	0.86	0.85	0.83	0.82	0.81	0.77	0.74	0.71	0.68
25.8	872	4101	1250	0.89	0.88	0.86	0.85	0.84	0.80	0.77	0.74	0.71
26.6	899	3281	1000	0.92	0.91	0.90	0.88	0.87	0.84	0.80	0.77	0.74
27.4	926	2461	750	0.95	0.94	0.93	0.91	0.90	0.87	0.84	0.80	0.77
28.3	954	1640	500	0.98	0.97	0.96	0.94	0.93	0.90	0.87	0.83	0.80
29.1	983	820	250	1.00	1.00	0.99	0.98	0.96	0.93	0.90	0.87	0.83
29.5	995	492	150	1.00	1.00	1.00	0.99	0.98	0.94	0.91	0.88	0.85
30.0	1012	0	0	1.00	1.00	1.00	1.00	0.99	0.96	0.93	0.90	0.87
			°C	20	25	30	35	40	45	50	55	60
			°F	68	77	86	95	104	113	122	131	140
			Air filter inlet temperature									

* Based on SAE standard ambient pressure vs. altitude. Assumes LT return temperature is 10°C above air filter inlet.

Temperature & altitude derate

1. Determine derate multiplier vs. temperature and altitude in Table A depending upon your operating condition.
2. Assumes the LT return temperature is 10°C above the air filter inlet with a maximum LT temperature of 50°C.
3. If the LT temperature exceeds 50°C, consult factory for recommendations.
4. Altitude is based upon SAE standard ambient pressure vs. altitude. For low barometric conditions add 150 m (500 ft) to site altitude.

Methane number capability

Load (percent of rated)			
100%	90%	75%	50%
78	69	54	45

Heat rejection factor (altitude and ambient) for HT and LT circuits

Barometer		Altitude		Table B Multiplier for HT & LT heat rejection vs alt & temp									
In Hg	mbar	Feet	Meters										
20.7	701	9843	3000	1.11	1.13	1.14	1.15	1.17	1.18	1.19	1.20	1.22	
21.4	723	9022	2750	1.10	1.12	1.13	1.14	1.15	1.17	1.18	1.19	1.21	
22.1	747	8202	2500	1.09	1.10	1.12	1.13	1.14	1.16	1.17	1.18	1.20	
22.8	771	7382	2250	1.08	1.09	1.11	1.12	1.13	1.14	1.16	1.17	1.18	
23.5	795	6562	2000	1.07	1.08	1.09	1.11	1.12	1.13	1.15	1.16	1.17	
24.3	820	5741	1750	1.06	1.07	1.08	1.10	1.11	1.12	1.14	1.15	1.16	
25.0	846	4921	1500	1.05	1.06	1.07	1.09	1.10	1.11	1.12	1.14	1.15	
25.8	872	4101	1250	1.04	1.05	1.06	1.07	1.09	1.10	1.11	1.13	1.14	
26.6	899	3281	1000	1.02	1.04	1.05	1.06	1.08	1.09	1.10	1.12	1.13	
27.4	926	2461	750	1.01	1.03	1.04	1.05	1.07	1.08	1.09	1.10	1.12	
28.3	954	1640	500	1.00	1.02	1.03	1.04	1.05	1.07	1.08	1.09	1.11	
29.1	983	820	250	0.99	1.00	1.02	1.03	1.04	1.06	1.07	1.08	1.10	
29.5	995	492	150	0.99	1.00	1.01	1.03	1.04	1.05	1.06	1.08	1.09	
30.0	1012	0	0	0.98	0.99	1.01	1.02	1.03	1.05	1.06	1.07	1.08	
				°C	20	25	30	35	40	45	50	55	60
				°F	68	77	86	95	104	113	122	131	140
Air filter inlet temperature													

LT & HT circuit heat rejection calculation

1. Determine derate multiplier vs. temperature derate per above.
2. Using the multiplier from #1 above as the percent load factor determine the heat rejection from the previous page.
3. From Table B find the HT and LT circuit multiplier.
4. Multiply the result of step 2 by the result of step 3 to obtain the heat rejection at your altitude and temperature.

Alternator data

Voltage range	Connection configuration	Temp rise °C	Duty ¹¹ cycle	Single phase factor	Alternator data sheet	Feature code
380-416	Wye, 3 Phase	105	C	N/A	333	B831-2
440-480	Wye, 3 Phase	105	C	N/A	331	B832-2
480	Wye, 3 Phase	105	C	N/A	331	B583-2
440-480	Wye, 3 Phase	125	C	N/A	331	B650-2
600	Wye, 3 Phase	105	C	N/A	331	B582-2
12470-13800	Wye, 3 Phase	80	C	N/A	521	B591-2
4160	Wye, 3 Phase	80	C	N/A	324	B590-2
4160	Wye, 3 Phase	105	C	N/A	323	B834-2

Continuous rating definition

Applicable for supplying power continuously to a constant load up to the full output rating for unlimited hours. No sustained overload capability is available for this rating. Consult authorized distributor for rating (equivalent to continuous power in accordance with ISO8528, ISO3046, AS2789, DIN6271, and BS5514). This rating is not applicable to all generator set models.

Note:

1. Weights and set dimensions represent a generator set with its standard features only. See outline drawing for other configurations.
2. At ISO3046 reference conditions, altitude 1013 mbar (30 in Hg), air inlet temperature 25°C (77°F).
3. Nominal performance +/- 2 1/2%.
4. According to ISO 3046/I with fuel consumption tolerance of +5% -0%.
5. Production variation/tolerance ±10%.
6. With air intake at 25°C (77°F). Tolerance ± 5°F.
7. Tested using pipeline natural gas with LHV of 33.44 MJ/Nm³ (905 BTU/ft³).
8. Outlet temperature controlled by thermostat, inlet temperature for reference only.
9. Inlet temperature controlled by thermostat, outlet temperature for reference only.
10. With engine driven coolant pump.
11. Standby (S), Prime (P), Continuous (C).
12. Maximum rated starting kVA that results in minimum of 90% of rated sustained voltage during starting.
13. Tolerance +/- 15%.
14. Exhaust system back pressure is a rated load and will decrease at lower loads.

**For more information contact your local Cummins distributor
or visit power.cummins.com**

Our energy working for you.™

