



# Exhaust Emission Data Sheet

## C22 N6

### 60 Hz Spark Ignited Generator Set

### EPA Emissions

**Engine Information:**

Model:	QSJ2.4	Bore:	3.41 in. (86.5 mm)
Type:	4 Cycle, In-line, 4 Cylinder	Stroke:	3.94 in. (100 mm)
Aspiration:	Naturally aspirated	Displacement:	146.46 cu. in. (2.4 liters)
Compression Ratio:	9.5:1		
Emission Control Device:	Electronic Air/Fuel Ratio Control and Closed-Loop Breather System		

<b>PERFORMANCE DATA</b>	<b>Natural Gas Standby</b>	<b>Propane Standby</b>
BHP @ 1800 RPM (60 Hz)	40	43.5
Fuel Consumption (SCFH)	278.8	112.7
Air to Fuel Ratio	16.5	14.7
Exhaust Gas Flow (CFM)	149.7	135.9
Exhaust Gas Temperature (°F)	1265	1300
<b>EXHAUST EMISSION DATA</b>		
HC (Total Unburned Hydrocarbons)*	100	525
NOx (Oxides of Nitrogen as NO <sub>2</sub> )	1599	1617
CO (Carbon Monoxide)	9689	14584
Values are ppmvd		
HC (Total Unburned Hydrocarbons)*	0.16	0.74
NOx (Oxides of Nitrogen as NO <sub>2</sub> )	6.27	5.91
CO (Carbon Monoxide)	26.80	37.54
Values are Grams per HP-Hour		
*HC includes all NMHC, VOC, POC, and ROC constituents (Non-Methane HC, Volatile Organic Compounds, Precursor Organic Compounds, and Reactive Organic Compounds)		

**TEST CONDITIONS**

Data was recorded during steady-state rated engine speed (± 25 RPM) with full load (±2%). Pressures, temperatures, and emission rates were stabilized.

**Fuel Specification:**

Natural Gas: Dry gas as received from Supplier (1000 BTU/SCF).  
 Propane: Meets the requirements for Commercial Grade Propane under the ASTM D1835 Standard Specification for Liquefied Gases

Fuel Temperature 60 ± 9 °F at Flow Transmitter

Fuel Pressure 14.73PSIA ± 0.5 PSIA at Flow Transmitter

Intake Air Temperature: 77 ± 9 °F at inlet

Barometric Pressure: 29.92 in. Hg ± 1 in. Hg

Humidity: NOx measurement corrected to 75 grains H<sub>2</sub>O/lb dry air

The NOx, HC, and CO emission data tabulated here were from a single engine under the test conditions shown above. These data are subjected to instrumentation and engine-to-engine variability. Field emission test data are not guaranteed to these levels. Actual field test results may vary due to test site conditions, installation, fuel specification, test procedures and instrumentation. Engine operation with excessive air intake or exhaust restriction beyond published maximum limit, or with improper maintenance, may result in elevated emission levels.